

Полумаски с одним фильтром Polimask GAMMA, GAMMA/Silicone

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: eut@nt-rt.ru || сайт: <https://ekastu.nt-rt.ru>



Order no.: 433 220

Product designation:

Half Mask Polimask GAMMA

In connection with respiratory filter of the series 230 (special thread 95mm) as filtering device.

The scope of protection is determined by the product information, technical standards and valid application rules.



DESCRIPTION

- Adaptability to any kind of face with a good sealing ability
- Anatomically shaped mask body made of non-irritating, soft EPDM
- Low breathing resistance
- Compatible with the use of glasses and goggles
- Easy donning and doffing
- Easy maintenance, washing and disinfection

MAIN FEATURES



PERFORMANCES



Comfort



Ergonomics



Sturdiness



Easy maintenance

APPLICATION FIELDS



Industry



Hospital



Chemical Pharmaceutical Industry



Agriculture

MATERIALS

- Faceblank: Ethylene-Propylene-Diene-Mixture (EPDM)
- Fastener for head harness: Plastic (ABS)
- Harness: Textile elastic band / Polypropylene (PP)
- Inhalation valve: Rubber
- Exhalation valve: Rubber
- Exhalation valve fit: Plastic (ABS)
- Connector: Polypropylene (PP)

WEIGHT

- approx.: 160 g

MARKING

- Trade mark of manufacturer (LOGO)
- Product designation
- Applied standard
- Manufacture year and -month
- CE-Identification
- Notified body
- Type identifying marking

DONNING AND USING

- Take the Half mask from the Packing and/or Storage container directly before use
- Use the Half mask in accordance with the information brochure

STORAGE

- Ambient temperature. Protect against cold, heat and humidity
- Consider conditions noted on the packaging

CERTIFICATIONS

- The mask is certified according to EN 140
- For use with particle, gas and combined filter of the series 230 (special thread 95mm)
- Certified according to European Regulation (EU) 2016/425

USER REFERENCES

EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those, which are reached in practice. The user must read and understand all functional information. Use the Respiratory protective devices with this information brochure, the relevant valid statutory regulations and the safety requirements of the profession associations, particularly the regulations for use in accordance with DGUV Rule 112-190 resp. DIN EN 529 „Respiratory protective devices – recommendation for selection, use, care and maintenance – guidelines“.



Order no.: 433 227

Product designation:

Half Mask Polimask GAMMA/Silicone

In connection with respiratory filter of the series 230 (special thread 95mm) as filtering device.

The scope of protection is determined by the product information, technical standards and valid application rules.



DESCRIPTION

- Adaptability to any kind of face with a good sealing ability
- Anatomically shaped mask body made of high-quality silicone, which is particularly kind to the skin
- Low breathing resistance
- Compatible with the use of glasses and goggles
- Easy donning and doffing
- Easy maintenance, washing and disinfection

MAIN FEATURES



PERFORMANCES



Comfort



Ergonomics



Sturdiness



Easy maintenance

APPLICATION FIELDS



Industry



Hospital



Chemical Pharmaceutical
Industry



Agriculture

MATERIALS

- Faceblank: Silicone
- Fastener for head harness: Plastic (ABS)
- Harness: Textile elastic band / Polypropylene (PP)
- Inhalation valve: Rubber
- Exhalation valve: Rubber
- Exhalation valve fit: Plastic (ABS)
- Connector: Polypropylene (PP)

WEIGHT

- approx.: 165 g

MARKING

- Trade mark of manufacturer (LOGO)
- Product designation
- Applied standard
- Manufacture year and -month
- CE-Identification
- Notified body
- Type identifying marking

DONNING AND USING

- Take the Half mask from the Packing and/or Storage container directly before use
- Use the Half mask in accordance with the information brochure

STORAGE

- Ambient temperature. Protect against cold, heat and humidity
- Consider conditions noted on the packaging

CERTIFICATIONS

- The mask is certified according to EN 140
- For use with particle, gas and combined filter of the series 230 (special thread 95mm)
- Certified according to European Regulation (EU) 2016/425

USER REFERENCES

EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those, which are reached in practice. The user must read and understand all functional information. Use the Respiratory protective devices with this information brochure, the relevant valid statutory regulations and the safety requirements of the profession associations, particularly the regulations for use in accordance with DGUV Rule 112-190 resp. DIN EN 529 „Respiratory protective devices – recommendation for selection, use, care and maintenance – guidelines“.

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: eut@nt-rt.ru || сайт: <https://ekastu.nt-rt.ru>